

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0797581149](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Micro-Lock PLUS Female-to-Micro-Lock PLUS Female, Tin Plated, 300.00mm, 26 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Lock PLUS Crimp Terminal
Datasheet Order No	987651-2631
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Micro-Lock PLUS
UPC	191130056484

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.701/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.78-1.02mm
Wire Size AWG	26
Wire/Cable Type	UL 1061

Material Info

Reference - Drawing Numbers

Sales Drawing 797581148-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[79758 Series](#)

Use With

[Micro-Lock PLUS Receptacle Housing
505565](#)