11mm Magnetic Connector, 4mm Right-Angle Sheathed Banana Jack


CT3885-#



Features:

- Voltage Max 1000 V CAT III / 600 V CAT IV
- Current Max 4 A
- Max Temperature 80 °C (176 °F)
- Insulation Material Polypropylene (PP)
- Magnet N35 / 1.2 Tesla
- RoHS 2 Compliant

Measurement Drawing: (not to scale)



Description:

The 3800 series of Magnetic Connectors facilitates a quick and reliable way to connect to terminal block screws or any other ferromagnetic conductors. These connectors provide ample magnetic hold for hands-free operation.



Order Information:

CT3885-#

11mm Magnetic Connector, 4mm Right-Angle Sheathed Banana Jack

• Color - replace '-#' with dash number: • Black, -2 Red, -6 Blue, -9 White

Contact Info:

Phone: 714-221-9330

Toll Free: 800-572-1028 (US Only)

Fax: 714-921-9849 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610 USA www.caltestelectronics.com

 ϵ

Copyright © 2019, Cal Test Electronics, Inc. All rights reserved. Information in this publication supersedes that in all previously published material. Trade names referenced are the service marks, trademarks of their respective companies.

