



22W

VT-2207 22W LED SLIM PANEL LIGHT COLORCODE:3000K ROUND

| | | |
|-----------------------|--------------------------|----------------------------------|
| Lumens 1800 | Beam Angle 120 | Dimensions Ø240 x 12mm |
|-----------------------|--------------------------|----------------------------------|

Warm White
SKU:6422

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

| | | | |
|----------------|---------------|------------------------|----------------------|
| Instant Start: | 0-100% in 11s | IP Rating: | IP20 |
| Watts: | 22 | Dimmable: | No |
| Lumens: | 1800 | Warranty (Years): | 2 |
| Shape: | Round | PF: | >0.9 |
| Beam Angle: | 120 | CRI: | >80 |
| Unit Color: | White | Operation Temperature: | -25 to +50°C |
| Body Type: | Aluminium | Input Power: | AC 85-265V, 50/60 Hz |
| Long life: | 20,000 Hours | Sensor Compatibility: | Yes |
| LED Chip Type: | SMD | | |

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| | |
|----------------------|----------|
| Gross Weight(GW) Kgs | 0.667 |
| Length(Box)mm | 260 |
| Width(Box)mm | 320 |
| Height(Box)mm | 30 |
| Unit CBM | 0.002496 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157626941 |
| Commodity Code | 9405403990 |

Master Box Packaging

| | |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 20 |
| Qty Per Pallet | 480 |

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES