

## Fabric label sheet - BMK 20X 8 YE - 5031388

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Fabric label sheet, Sheet, yellow, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: adhesive, lettering field size: 20 mm x 8 mm, Number of individual labels: 270




### Your advantages

- Available in various dimensions
- Self-adhesive labels for labeling by hand or with a plotter
- Labeling service: Phoenix Contact can custom-label all BMK ... markers according to your requirements
- Secure adhesion even on curved or uneven surfaces as well as round corners
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking".



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 095413
GTIN	4017918095413
Weight per Piece (excluding packing)	10.600 g
Custom tariff number	39199080
Country of origin	Belgium

### Technical data

#### Dimensions

Length (b)	8 mm
Width (a)	20 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

#### General

Note	Can be labeled with CMS
Color	yellow

# Fabric label sheet - BMK 20X 8 YE - 5031388

## Technical data

### General

Base element material	Polyester foil
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	Polyester foil
Number of individual labels	270
Number of individual labels per row	9
Adhesive	Acrylic
Printability	Plotter
Device	5144615 CMS-P1-PLOTTER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	adhesive

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

## Fabric label sheet - BMK 20X 8 YE - 5031388

### Classifications

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

#### Printing system accessories

Accessories - CMS-P1-PAD - 5144819



Accessories