

Marker pin - BNB-TRK - 2701417

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker pin, Stud, white, can be labeled with: Marker pen, mounting type: plug in, for terminal block width: 7.5 mm, lettering field size: 4 x 7.5 mm

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	0.060 g
Custom tariff number	49119900
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	4 mm
Width (a)	7.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Please specify the required marking with order.
Color	white
Base element material	PA
Type	high
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN 30646
	DIN VDE 0611-1
Marking mounting type	plug in

Marker pin - BNB-TRK - 2701417

Technical data

Standards and Regulations

Wipe resistance	DIN 30646
	DIN VDE 0611-1
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505