

Conductor marking collar - UCT-WMS 4,7 (12X5,5) YE - 0828573

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: slide-on, for terminal block width: 5.2 mm, cable diameter range: 2.5 ... 4.7 mm, lettering field size: 12 x 5.5 mm, Number of individual labels: 45

Your advantages

- The UCT-WMS ... UniCard labeling range includes markers that can be threaded onto conductors
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the THERMOMARK CARD and the BLUEMARK LED
- The markers support multi-line labeling
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts

Key Commercial Data

Packing unit	6 pc
Minimum order quantity	6 pc
GTIN	 4 046356 519700
GTIN	4046356519700
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	12 mm
Width (a)	5.5 mm
Height (c)	7.1 mm
Cable diameter	2.5 mm ... 4.7 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Conductor marking collar - UCT-WMS 4,7 (12X5,5) YE - 0828573

Technical data

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---------------------------------------------------------------------------------------------------------

General

Note	Can be labeled via thermal transfer
Color	yellow
Type	Card form
Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	PC V0
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	45
Number of individual labels per row	9
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	32.4 %
R22	HL 1 - HL 3
R23	HL 1 - HL 3
R24	HL 1 - HL 3

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	-----------------------------------------------------------------------------------------------------

Conductor marking collar - UCT-WMS 4,7 (12X5,5) YE - 0828573

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG3 - 5146613



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-WMS...)

Conductor marking collar - UCT-WMS 4,7 (12X5,5) YE - 0828573

Accessories

Magazine - P1 UC-MAG 7 - 5146568

Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating: UC-WMCO...



Magazine - TMP-UCT-MAG3 - 0803344

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMS...



Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>