

Coupling relay - PSR-PS20-1NO-1NC-24DC-DUMMY - 2702346

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Coupling relay for SIL 3 high and low-demand applications, couples digital output signals to the I/O, 1 enabling current path, 1 confirmation current path, 1 digital signal output, safe state off applications, test pulse filter, fixed screw terminal block

The figure shows the standard type



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 129709
GTIN	4055626129709
Weight per Piece (excluding packing)	48.700 g
Custom tariff number	90230080
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Input data

Rated control circuit supply voltage U_s	24 V DC
--	---------

Output data

Contact type	1 enabling current path
	1 confirmation current path

General

Net weight	48.7 g
------------	--------

Connection data

Connection method	Screw connection
pluggable	no

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	--

Coupling relay - PSR-PS20-1NO-1NC-24DC-DUMMY - 2702346

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 4.0	40020600
eCl@ss 4.1	40020600
eCl@ss 5.0	27371900
eCl@ss 5.1	27371900
eCl@ss 6.0	27371800
eCl@ss 7.0	27371819
eCl@ss 8.0	27371819
eCl@ss 9.0	27371819

ETIM

ETIM 5.0	EC001449
ETIM 6.0	EC001449
ETIM 7.0	EC001449

UNSPSC

UNSPSC 13.2	39121501
UNSPSC 18.0	39122205
UNSPSC 19.0	39122205
UNSPSC 20.0	39122205
UNSPSC 21.0	39122205