
WIRING MAP					
Jl	COLOR	J2	J3	J4	
1	BLUE	12			
2	ORANGE	11			
3	GREEN	10			
4	BROWN	9			
5	GRAY		12		
6	WHITE		11		
7	RED		10		
8	BLACK		9		
9	YELLOW			12	
10	PURPLE			11	
11	ROSE			10	
12	AQUA			9	
13	BLUE/BLACK	4			
14	ORANGE/BLACK	3			
15	GREEN/BLACK	2			
16	BROWN/BLACK	1			
17	GRAY/BLACK		4		
18	WHITE/BLACK		3		
19	RED/BLACK		2		
20	BLACK / WHITE		1		
21	YELLOW/BLACK			4	
22	PURPLE/BLACK			3	
23	rose/black			2	
24	AQUA/BLACK			1	

	REVISIONS		
REV	DESCRIPTION	DATE	APPROVED
Α	REV A DRAWING RELEASED	03/28/19	PHOSPODAR



PART NUMBER	METERS (FEET)
MPM24-MPM308OM4R-1	1.0 (3.28)
MPM24-MPM308OM4R-3	3.0 (9.84)
MPM24-MPM308OM4R-5	5.0 (16.40)
MPM24-MPM308OM4R-10	10.0 (32.81)



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.