

Interface module - UM-D25SUB-F/KDS3-PMT/SC061 - 2906274


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with 25-pos. D-SUB socket strip and screw connection with knife disconnection, for mounting on NS 35/7,5 or NS 32



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 055626 057316
GTIN	4055626057316
Weight per Piece (excluding packing)	300.000 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	138 mm
Height	90 mm
Depth	59 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Maximum altitude	≤ 2000 m
Degree of protection	IP00
	≥ IP54 (Installation location)

General

Nominal voltage U_N	25 V AC
	60 V DC

Interface module - UM-D25SUB-F/KDS3-PMT/SC061 - 2906274

Technical data

General

Max. perm. current (per branch)	2 A
Max. permissible current (all branches)	4 A
Number of positions	25
Mounting position	any

Connection data

Connection name	Field level
Connection method	Screw connection with disconnect knife
Number of positions	25
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Connection data 2

Connection name	Controller level
Connection method	D-SUB-25 female connector
Number of connections	1
Number of positions	25

Standards and Regulations

Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178: 1998-04
Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 µs)
Insulation	Functional insulation
Pollution degree	2
Overvoltage category	II

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27141152

Interface module - UM-D25SUB-F/KDS3-PMT/SC061 - 2906274

Classifications

eCl@ss

eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 5.0	EC002780
ETIM 6.0	EC002780
ETIM 7.0	EC002780

UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121432
UNSPSC 19.0	39121432
UNSPSC 20.0	39121432
UNSPSC 21.0	39121432