

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Stripping and crimping machine, 120-230 V input voltage, electro-pneumatic, for loose ferrules with insulating collar, 4 mm², 6 mm², and 10 mm², without conversion kit

Your advantages

- ✓ Quick change of cross section without the need for additional adjustments
- ✓ Up to 1200 conductors can be processed an hour
- ✓ Suitable for bulk processing
- ✓ Rugged design
- ✓ The pull-out forces meet the requirements of IEC/EN 60999 and IEC/EN 60947
- ✓ The stripping and crimping machine can be used to process loose ferrules with insulating collars according to DIN 46228-4
- ✓ The conductor is stripped in a single step and crimped with a ferrule to a high standard of quality
- ✓ Quantity counter



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 526883
GTIN	4046356526883
Weight per Piece (excluding packing)	28,500.000 g
Custom tariff number	84798100
Country of origin	Germany

Technical data

Dimensions

Length (b)	550 mm
Width (a)	250 mm
Height (c)	412 mm
Stripping length	15.5 mm

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Technical data

General

Compression	trapezoidal
Pressure range	5 bar ... 6 bar
Air consumption per compression	1.2 l
Power consumption	70 W
Test standard	DIN 46228-4: 1990-09
Insertion length minimum	40 mm
Weight	29 kg
Min. cross section	4 mm ²
Max. cross section	10 mm ²

Standards and Regulations

Test standard	DIN 46228-4: 1990-09
---------------	----------------------

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	17130101
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	17130100
eCl@ss 6.0	17130100
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101
eCl@ss 9.0	17130101

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC002778
ETIM 6.0	EC002778
ETIM 7.0	EC002778

UNSPSC

UNSPSC 6.01	30211811
-------------	----------

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01549
-----	--	--------------------------

Accessories

Accessories

Conversion kit

Conversion kit - CF 1000-10-TOOLKIT 4/10-12 - 1212458



Conversion kit for CF 1000-10, for insulated ferrules according to DIN 46228-4: 1990-09, cross section range: 4 mm², stripping length: 10 - 12 mm

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Conversion kit - CF 1000-10-TOOLKIT 6/12 - 1212459



Conversion kit for CF 1000-10, for insulated ferrules according to DIN 46228-4: 1990-09, cross section range: 6 mm², stripping length: 12 mm

Conversion kit - CF 1000-10-TOOLKIT 10/12 - 1212460



Conversion kit for CF 1000-10, for insulated ferrules according to DIN 46228-4: 1990-09, cross section range: 10 mm², stripping length: 12 mm

Die

Replacement die - CF 1000 PB 4-10 - 1212668

Accessories for CF 1000 and CF 1000-10 stripping and crimping machine, crimping jaw for 4.0 mm² sleeves and 10 mm sleeve length



Accessories for tools/automatic devices - CF 1000-10 PB 4-12 - 1212669

Accessories for CF 1000 and CF 1000-10 stripping and crimping machines, crimping jaw for 4.0 mm² sleeves and 12 mm sleeve length



Accessories for tools/automatic devices - CF 1000-10 PB 6-12 - 1212670

Accessories for CF 1000-10 stripping and crimping machine, crimping jaw for 6.0 mm² sleeves and 12 mm sleeve length



Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Accessories for tools/automatic devices - CF 1000-10 PB 10-12 - 1212671

Accessories for CF 1000-10 stripping and crimping machine, crimping jaw for 10.0 mm² sleeves and 12 mm sleeve length



Fuse

Accessories for tools/automatic devices - CF 1000 SICHERUNG - 1207190



Accessories for CF 1000 stripping and crimping machine, mains fuse, 20 x 5 mm, slow-blow, 2 A, up to 250 V

Replacement fuse - FUSE SB 2.0A/250V - 1212685



Accessories for stripping and crimping device CF 1000-1,5 and CF 1000-10, mains fuse, 20 x 5 mm, slow-blow, 2 A, up to 250 V

Housing

Housing cover - CF 1000-COVER - 1208306



Protective cover, for CF 1000

Knife

Spare knife - CF 1000 EM4,0 - 1212663



Accessories for CF 1000 and CF 1000-10 stripping and crimping machine, replacement blade for 4.0 mm², V-shaped

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Spare knife - CF 1000-10 EM6,0 - 1212664



Accessories for CF 1000-10 stripping and crimping machine, replacement blade for 6.0 mm², V-shaped

Spare knife - CF 1000-10 EM10 - 1212665



Accessories for CF 1000-10 stripping and crimping machine, replacement blade for 10.0 mm², V-shaped

Mounting material

Accessories for tools/automatic devices - CF 1000 LZT4,0 - 1207093



Accessories for CF 1000 and CF 1000-10 stripping and crimping machine, litz wire centering device for 4.0 mm²

Accessories for tools/automatic devices - CF 1000-10 LZT6,0 - 1212661



Accessories for CF 1000-10 stripping and crimping machine, litz wire centering device for 6.0 mm²

Accessories for tools/automatic devices - CF 1000-10 LZT10 - 1212662



Accessories for CF 1000-10 stripping and crimping machine, litz wire centering device for 10.0 mm²

Separation

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Accessories for tools/automatic devices - CF 1000 SORT4,0 - 1206887



Accessories for CF 1000-1,5 and CF 1000-10 stripping and crimping devices, feeder bowl for 2.5 mm² and 4.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000 VEP4,0 - 1206942



Accessories for CF 1000 and CF 1000-10 stripping and crimping machine, separating plate for 4.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000-10 SORT6,0 - 1212652



Accessories for CF 1000-10 stripping and crimping machine, feeder bowl for 6.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000-10 SORT10 - 1212653



Accessories for CF 1000-10 stripping and crimping machine, feeder bowl for 10.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000-10 VEP6,0 - 1212654



Accessories for CF 1000-10 stripping and crimping device, separation plate for 6.0 mm² sleeves

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Accessories for tools/automatic devices - CF 1000-10 VEP10 - 1212655



Accessories for CF 1000-10 stripping and crimping device, separation plate for 10.0 mm² sleeves

Sleeve receiver

Accessories for tools/automatic devices - CF 1000 HWB4,0 - 1206968



Accessories for CF 1000 and CF 1000-10 stripping and crimping machine, sleeve reversing block for 2.5 - 4.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000 HA4,0 - 1207048



Accessories for CF 1000-1,5 stripping and crimping device up to serial number 160591 and CF 1000-10, sleeve receiver for 4.0 mm² sleeve

Accessories for tools/automatic devices - CF 1000-10 HWB6,0 - 1212656



Accessories for CF 1000-10 stripping and crimping machine, sleeve reversing block for 6.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000-10 HWB10 - 1212658



Accessories for CF 1000-10 stripping and crimping machine, sleeve reversing block for 10.0 mm² sleeves

Crimping tool, electro-pneumatic - CF 1000-10 - 1212456

Accessories

Accessories for tools/automatic devices - CF 1000-10 LOC6,0 - 1212659



Accessories for CF 1000-10 stripping and crimping machine, sleeve receiver element for 6.0 mm² sleeves

Accessories for tools/automatic devices - CF 1000-10 LOC10 - 1212660



Accessories for CF 1000-10 stripping and crimping machine, sleeve receiver element for 10 mm² sleeves
