


Replacement die - CF 500/DIE RCT 10-2 - 1212246

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die for crimping machine CF 500, for tube lugs 4 ... 10 mm², 4 mm²: Outer Ø 5 mm, Inner Ø 3 mm, 6 mm²: Outer Ø 6.5 mm, Inner Ø 3.8 mm, 10 mm²: Outer Ø 6 mm, Inner Ø 4.5 mm

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 450041
GTIN	4046356450041
Weight per Piece (excluding packing)	65.200 g
Custom tariff number	84799070
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Cable diameter	2.4 mm ... 3.7 mm
----------------	-------------------

General

Color	silver
Compression	Indent crimp
Min. cross section	4 mm ²
Max. cross section	10 mm ²

Classifications

eCl@ss

eCl@ss 10.0.1	17139201
eCl@ss 4.0	21043000
eCl@ss 4.1	21043000

Replacement die - CF 500/DIE RCT 10-2 - 1212246

Classifications

eCl@ss

eCl@ss 5.0	21059000
eCl@ss 5.1	21059000
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	17139201

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01549
-----	--	--------------------------

