

Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Die, for Crimpfox-M, for turned contacts 0.5 ... 4 mm², packed in a serial storage box

Your advantages

- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ For CK 2,5 ED..., CK 4,0 ED... turned pin and socket contacts

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 452540 |
| GTIN | 4046356452540 |
| Weight per Piece (excluding packing) | 73.600 g |
| Custom tariff number | 82032000 |
| Country of origin | Sweden |

Technical data

Dimensions

| | |
|------------|---------|
| Length (b) | 114 mm |
| Width (a) | 75 mm |
| Height (c) | 25.5 mm |

General

| | |
|--------------------|---------------------|
| Color | black |
| Compression | Square crimp |
| Type of contact | Turned contacts |
| Designation | Crimping position 1 |
| Min. cross section | 0.5 mm ² |
| Max. cross section | 1 mm ² |
| AWG min | 20 |
| AWG max | 18 |
| Designation | Crimping position 2 |
| Max. cross section | 1.5 mm ² |

Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

Technical data

General

| | |
|--------------------|---------------------|
| AWG max | 16 |
| Designation | Crimping position 3 |
| Max. cross section | 2.5 mm ² |
| AWG max | 14 |
| Die station | Crimping position 4 |
| Max. cross section | 4 mm ² |
| AWG max | 12 |
| Weight | 72 g |
| Min. cross section | 0.5 mm ² |
| Max. cross section | 4 mm ² |
| AWG min | 20 |
| AWG max | 12 |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 21019290 |
| eCl@ss 4.0 | 21040300 |
| eCl@ss 4.1 | 21040300 |
| eCl@ss 5.0 | 21040300 |
| eCl@ss 5.1 | 21040300 |
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21019290 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |
| ETIM 6.0 | EC001282 |
| ETIM 7.0 | EC001282 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11 | 23171604 |
| UNSPSC 12.01 | 27111518 |
| UNSPSC 13.2 | 27111518 |
| UNSPSC 19.0 | 27111518 |

Replacement die - CRIMPFOX-M TC 4/DIE - 1212075

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|--------------------------|
| EAC |  | RU x- DE.xx08.B.02974 |
|-----|---|--------------------------|
