

## Tool set - SF-SL/PH SET - 1212541

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver set, bladed/crosshead Phillips Recess<sup>®</sup>, 6-part, incl. rack

### Your advantages

- The SF-SL ... screwdriver sets are available with a variety of contents
- Wall-mountable screwdriver rack included

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589765
GTIN	4046356589765
Weight per Piece (excluding packing)	624.900 g
Custom tariff number	82054000
Country of origin	Czech Republic

### Technical data

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Articles in set

Screwdriver - SF-SL 0,5X3,0-80 - 1212548



Screwdriver, slot-headed, size: 0.5 x 3.0 x 80 mm, 2-component grip, with non-slip grip

## Tool set - SF-SL/PH SET - 1212541

### Articles in set

Screwdriver - SF-SL 0,8X4,0-100 - 1212551



Screwdriver, bladed (lasered), size: 0.8 x 4.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SF-SL 1,0X5,5-150 - 1212552



Screwdriver, bladed (lasered), size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

Screwdriver - SF-SL 1,2X6,5-150 - 1212553



Screwdriver, bladed (lasered), size: 1.2 x 6.5 x 150 mm, 2-component grip, with non-slip grip

Philips screwdriver - SF-PH 1-80 - 1212559



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 1 x 80, 2-component grip, with non-slip grip

Philips screwdriver - SF-PH 2-100 - 1212560



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

### Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21040200

# Tool set - SF-SL/PH SET - 1212541

## Classifications

### eCl@ss

eCl@ss 4.1	21040200
eCl@ss 5.0	21040200
eCl@ss 5.1	21040200
eCl@ss 6.0	21040200
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

### ETIM

ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

