

## Cable marker label - WML 14 (25X19)A4 - 0830693

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker label, Sheet, white, unlabeled, can be labeled with: Office printing systems, mounting type: adhesive, cable diameter: ≤ 14 mm, lettering field size: 25 x 19 mm, Number of individual labels: 28




### Your advantages

- The cable marker labels consist of a self-adhesive marking field and a transparent protective foil
- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- Resistant to solvents



### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 10 pc                                                                                                   |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 046356 718783 |
| GTIN                                 | 4046356718783                                                                                           |
| Weight per Piece (excluding packing) | 15.000 g                                                                                                |
| Custom tariff number                 | 39199080                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 63.5 mm |
| Width (a)  | 25 mm   |

#### Ambient conditions

|                                 |                                                                                                         |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C                                                                                       |
| Recommended storage conditions  | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

#### General

## Cable marker label - WML 14 (25X19)A4 - 0830693

### Technical data

#### General

|                                                                     |                                                 |
|---------------------------------------------------------------------|-------------------------------------------------|
| Note                                                                | Print image may vary depending on laser printer |
| Color                                                               | white                                           |
| Base element material                                               | Vinyl film                                      |
| Type                                                                | Label                                           |
| Components                                                          | Free from halogen and cadmium                   |
| Material                                                            | Polyester                                       |
| RoHS compliant                                                      | Yes                                             |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)                     |
| Number of individual labels                                         | 28                                              |
| Number of individual labels per row                                 | 7                                               |
| Adhesive                                                            | Acrylic                                         |
| Printability                                                        | Office printing systems                         |
|                                                                     | Plotter                                         |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                            |
| Result                                                              | Test passed                                     |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03                    |
| Test duration                                                       | 96 h                                            |
| Result of weather resistance test                                   | Test passed                                     |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02                       |
| Test duration                                                       | 96 h                                            |
| Salt spray testing result                                           | Test passed                                     |
| Marking mounting type                                               | adhesive                                        |

#### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27400400 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |

## Cable marker label - WML 14 (25X19)A4 - 0830693

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC001530 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |