

Screw connection - WP-GA HF IP66 PG11 BK - 3240918


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Pg thread, IP66 protection, angled

RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 710251 |
| GTIN | 4046356710251 |
| Weight per Piece (excluding packing) | 10.200 g |
| Custom tariff number | 39174000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------------|---------------------|
| Length (b) | 37.5 mm |
| Width (a) | 23 mm |
| Height (c) | 42 mm |
| Diameter | 24.5 mm |
| Outside diameter | 15.8 mm |
| Cable diameter | 15.8 mm ... 15.8 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
| Degree of protection | IP66 |

General

| | |
|-------|--------|
| Color | black |
| Type | Angled |

Screw connection - WP-GA HF IP66 PG11 BK - 3240918

Technical data

General

| | |
|--|--|
| | Outer thread |
| Components | free from silicone, halogen, and cadmium |
| Flammability rating according to UL 94 | V2 |
| Material | PA |

Standards and Regulations

| | |
|--|-----|
| Halogen-free | yes |
| Connection in acc. with standard | UL |
| Flammability rating according to UL 94 | V2 |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141200 |
| eCl@ss 4.1 | 27141200 |
| eCl@ss 5.0 | 27149100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149109 |
| eCl@ss 8.0 | 27149109 |
| eCl@ss 9.0 | 27144432 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC001178 |
| ETIM 5.0 | EC001178 |
| ETIM 6.0 | EC000441 |
| ETIM 7.0 | EC000441 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121411 |
| UNSPSC 12.01 | 39121411 |
| UNSPSC 13.2 | 39121311 |
| UNSPSC 18.0 | 39121311 |
| UNSPSC 19.0 | 39121311 |
| UNSPSC 20.0 | 39121311 |

Screw connection - WP-GA HF IP66 PG11 BK - 3240918

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121311 |
|-------------|----------|

Approvals

Approvals

Approvals

LR / UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approval details

| | | |
|----|--|---|
| LR | | http://www.lr.org/en |
|----|--|---|

| | | |
|---------------|--|---|
| UL Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm |
|---------------|--|---|

| | | |
|------------------------|--|---|
| VDE Zeichengenehmigung | | http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx |
|------------------------|--|---|

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 15,8 BK - 3240682



Polyamide protective hose, inflammability class V0, UV resistant

Screw connection - WP-GA HF IP66 PG11 BK - 3240918

Accessories

Protective hose - WP-PA HF-HB 15,8 BK - 3240840



Polyamide protective hose, inflammability class HB, UV resistant

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>