

Plastic cable markers - KMK 5 - 0830746

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable binders, cable diameter range: 10 ... 40 mm, lettering field size: 60 x 15 mm



Your advantages

- ✓ Plastic cable markers for insert labels, for assembly with cable binders
- ✓ Plastic cable markers for marking and bundling conductors and cables indoors
- ✓ The markers have eyelets and are attached with cable binders
- ✓ The marked insert label is protected from dirt by the sealing cap

Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 738590
GTIN	4046356738590
Weight per Piece (excluding packing)	3.180 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	60 mm
Width (a)	15 mm
Height (c)	15 mm
Cable diameter	10 mm ... 40 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Plastic cable markers - KMK 5 - 0830746

Technical data

General

Color	transparent
Type	Mounting set
Components	free from silicone and halogen
Material	Polyethylene
Marking mounting type	Assembly with cable binders

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Device marking

Plastic cable markers - KMK 5 - 0830746

Accessories

Insert label - EMT (60X15)R - 0801846



Snap-in marker, for marking Inline modules

Snap-in markers - US-EMP (60X15) - 0828781



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 9

Labeled device marker

Insert label - EMT (60X15)R CUS - 0801998



Snap-in marker, for marking Inline modules

Snap-in markers - US-EMP (60X15) CUS - 0830052



Snap-in markers, can be ordered: By card, white, labeled according to customer specifications, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm

Terminal marking

Insert strip - ESL (60X15) - 0801851



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, mounting type: insert, lettering field size: 60 x 15 mm, Number of individual labels: 51
