


# Cable gland - UC-Z2019 - 1606833

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable gland, cable diameter range: 9.5 mm ... 14.5 mm



## Key Commercial Data

Packing unit	250 pc
Minimum order quantity	10 pc
GTIN	 4 046356 262194
GTIN	4046356262194
Weight per Piece (excluding packing)	36.700 g
Custom tariff number	74199990
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27260700
eCl@ss 5.0	27149100
eCl@ss 5.1	27260700
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121

## Cable gland - UC-Z2019 - 1606833

### Classifications

#### ETIM

ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311