


Product Specification Sheet

AC:220-240V, 50/60Hz



Technical Information

Holder Type: GU10 Dimmable: Rated Load: Max 35W Warranty (Years): Body Type: Aluminium Body + Clear PC Diffuser Operation Temperature: -20? to 45? IP Rating: Input Power:

Features

- Perfect replacement for traditional wall fittings
 - Designed with an Ingress protection of IP54
- Available body type options of Aluminium and Stainless Steel
- Suitable with GU10 base lights (Fitting only Light not included)
- Easy to Install and low maintenance
- Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

 Gross Weight(GW) Kgs
 1.56

 Unit CBM
 0.00648

Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 4

 Qty Per Pallet
 200

Listing Details

 EAN Code
 3800157636384

 Commodity Code
 9405109890





OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES