



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	REV A DRAWING RELEASED	04/16/2019	MMARTINEZ
B	ECN 10028: ADDED NOTE FOR CAT6A COMPLIANT	09/18/2019	MMARTINEZ



NOTES:

1. 10gig COUPLERS ARE CAT6A COMPLIANT.
2. DIMENSIONS FOR REFERENCE ONLY.
3. MATERIAL: .06 THICK COLD ROLLED STEEL.
4. PANEL FINISH: FLAT BLACK POWDER COAT.
5. SILKSCREEN COLOR: WHITE.
6. PANEL COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)  
 OVERALL CABLE LENGTH TOLERANCE:  
 ≤12 [305] ≤±0 [1.27] / -0  
 >12 [305] ≤±0 [1.27] / -0  
 >40 [1016] ≤±0 [1.27] / -0  
 >120 [3048] ≤±0 [1.27] / -0  
 >300 [7620] ≤±0 [1.27] / -0  
 ALL OTHER DIMENSIONAL TOLERANCES:  
 X = ±.2 [5.08]  
 XX = ±.02 [5.1]  
 XXX = ±.005 [1.3]


APPROVALS	DATE
DRAWN BY L DUNN	04/10/2019
CHECKED BY D PRISIELLO	04/10/2019
APPROVED BY MMARTINEZ	04/10/2019

**L-com** Global Connectivity  
 50 HIGH STREET  
 NORTH ANDOVER, MA  
 01845

CATEGORY: RACK PANELS

PRODUCT DESCRIPTION: PNL,2U V-RACK w/48 C6A CPLR+CM

SIZE	FSCM NO.	DWG. NO.	REV.
B	43321	PR35V-C6A-48-CM	B



CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  
 COLOR VARIATIONS MAY OCCUR