



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 08/13/2019 | MMARTINEZ |
| | | | |
| | | | |

| <u>QTY.</u> | <u>DESCRIPTION</u> |
|-------------|------------------------------------|
| 4 | #6 U-TYPE SPEED NUT |
| 4 | #6-32 X 1/2" LG SST PAN HEAD SCREW |

NOTES:

- KIT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031

| | | | |
|---|--|---|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE |  50 HIGH STREET NORTH ANDOVER, MA 01845 |
| | DRAWN BY DFRISIELLO | 08/13/2019 | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13] | CHECKED BY MMARTINEZ | 08/13/2019 | CATEGORY ENCLOSURE |
| | APPROVED BY MMARTINEZ | 08/13/2019 | |
| PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION VENT HARDWARE KIT FOR NB14/NB18 | |
| | COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 |
| | | DWG. NO. NB14-18-VHW-KIT | REV. A |
| | | SCALE: NONE | SHEET 1 OF 1 |