

Product Specification Sheet



Technical Information

Holder Type:	E27	IP Rating:	IP44
Rated Load:	Max 40W	Dimmable:	No
Unit Color:	MATT WHITE	Warranty (Years):	2
Body Type:	Aluminium + Glass	Input Power:	AC:220-240V,50Hz

Features

- / Traditional Garden Lamps designed to fit the Modern day requirements
- Available in different designs, shapes and sizes
- Waterproof Lamps available in series of IP rating from IP44 to IP54
- Easy to Install and low Maintenance
- Suitable with E27 base lights(Fitting only Light not included)
- Application: Suitable for Garden, Floor, Ceiling etc

Packaging

		Listing Details	
Gross Weight(GW) Kgs	1.18	EAN Code	3800157616249
Length(Box)mm	220	Commodity Code	9405109890
Width(Box)mm	150		
Height(Box)mm	260		
Unit CBM	0.008385		
Master Box Packaging			
Master Box Qty (Pcs Per Carton)	10		
Qty Per Pallet	180		

