



9W

VT-709 9W LED WALL LIGHT COLORCODE:3000K IP20 BLACK BODY

Lumens 990	Beam Angle 360	Dimensions 440x335x75mm
----------------------	--------------------------	-----------------------------------

Warm White
 SKU:8223

2 YEARS
 WARRANTY



Technical Information

Watts:	9	Dimmable:	No
Lumens:	990	Warranty (Years):	2
Beam Angle:	360	PF:	>0.45
Unit Color:	Black	CR:	>80
Body Type:	Aluminium	Operation Temperature:	-25 to +50°C
Long life:	20,000 Hours	Input Power:	AC:220-240V,50/60Hz
IP Rating:	IP20		

Features

- ✓ Perfect choice of Interior lightingin for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.115
Unit CBM	0.01786

Listing Details

EAN Code	3800157623407
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	80

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES