

12W

VT-812 12W LED WALL LAMP COLORCODE:4000K BLACK

| | | |
|----------------------|--------------------------|-----------------------------------|
| Lumens 960 | Beam Angle 100 | Dimensions 405x100x93mm |
|----------------------|--------------------------|-----------------------------------|

Day White
 SKU:8257




Technical Information

| | | | |
|----------------|-----------------|------------------------|----------------------|
| Instant Start: | 0-100% in 1/1s | IP Rating: | IP20 |
| Watts: | 12 | Dimmable: | No |
| Lumens: | 960 | Warranty (Years): | 3 |
| Beam Angle: | 100 | PF: | >0.5 |
| Unit Color: | Black | CRI: | >80 |
| Body Type: | Plastic + Metal | Operation Temperature: | -20 to +45°C |
| Long life: | 30,000 Hours | Input Power: | AC 220-240V, 50/60Hz |
| LED Chip Type: | SMD | Sensor Compatibility: | Yes |

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| | |
|----------------------|----------|
| Gross Weight(GW) Kgs | 0.718 |
| Length(Box)mm | 110 |
| Width(Box)mm | 410 |
| Height(Box)mm | 120 |
| Unit CBM | 0.005412 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157627078 |
| Commodity Code | 9405403990 |

Master Box Packaging

| | |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 12 |
| Qty Per Pallet | 240 |

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES