



5W

VT-825 5W LED WALL LIGHT COLORCODE:3000K -BLACK BODY

| | | |
|----------------------|--------------------------|-----------------------------------|
| Lumens 550 | Beam Angle 120 | Dimensions 170x170x75mm |
|----------------------|--------------------------|-----------------------------------|

Warm White
 SKU:8282



Technical Information

| | | | |
|----------------|--------------|------------------------|---------------------|
| Watts: | 5 | Dimmable: | No |
| Lumens: | 550 | Warranty (Years): | 2 |
| Beam Angle: | 120 | PF: | >0.5 |
| Unit Color: | Black | CRI: | >80 |
| Body Type: | Aluminium | Operation Temperature: | -20°C to +45°C |
| Long life: | 20,000 Hours | Input Power: | AC:220-240V,50/60Hz |
| LED Chip Type: | SMD | Sensor Compatibility: | Yes |
| IP Rating: | IP65 | | |

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| | |
|----------------------|-------|
| Gross Weight(GW) Kgs | 0.67 |
| Unit CBM | 0.004 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157629768 |
| Commodity Code | 9405403990 |

Master Box Packaging

| | |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 20 |
| Qty Per Pallet | 360 |

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES