



**Order symbol:** TPCM 131308  
**Product nbr:** 5824023  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074087089  
**EI. number:**  
**Finland:**

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	130	130	75	<b>Rating:</b> Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07/IK08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 Flammability Rating: UL 746C 5" Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 12
inch:	5.1	5.1	3.0	
<b>Materials:</b>				<b>Certificates:</b> SGS Fimko
<b>Material:</b>	Polycarbonate			
<b>Base colour:</b>	RAL 7035 -light grey			
<b>Cover screws material:</b>	Polyamide			
<b>Cover colour:</b>	RAL 7035 -light grey			
<b>Cover screws colour:</b>	Grey			
<b>Gasket material:</b>	Polyurethane			
<b>Temperatures:</b>				
<b>Temperature °C (short term):</b>	-40 ... 120 °C			
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			
<b>Temperature °F (short term):</b>	-40 ... 250 °F			
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			
<b>Accessories:</b>				
FP 10674				

