

TEMPO TPC 342912T



Order symbol: TPC 342912T
Product nbr: 5824009
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074086952
EI. number:
Finland:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	344	289	117	DR 316 ARH 2328 FP 10674
inch:	13.5	11.4	4.6	DIN-35 Mounting rail DIN-35 Mounting rail

Materials:	Rating:
Material: Polycarbonate	Ingress Protection (EN 60529): IP65
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07/IK08
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	Flammability Rating: UL 746C 5"
Gasket material: Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4, 4X, 12

Temperatures:	Certificates:
Temperature °C (short term): -40 ... 120 °C	SGS Fimko
Temperature °C (continuous): -40 ... 80 °C	
Temperature °F (short term): -40 ... 250 °F	
Temperature °F (continuous): -40 ... 175 °F	

Accessories:
MP 3429 Mounting plate

