



Order symbol: TPCM 090706
Product nbr: 5824020
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074064929
EI. number:
Finland:

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	95	65	60	
inch:	3.7	2.6	2.4	
Materials:				Rating:
Material:	Polycarbonate			Ingress Protection (EN 60529): IP65
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08
Cover screws material:	Polyamide			Electrical insulation: Totally insulated
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey			Flammability Rating: UL 746C 5"
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: NEMA 1, 4, 4X, 12
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			
Accessories:				
FP 10674				

