

LQP02HQ1N1W02#

*# indicates a package specification code.



< List of part numbers with package codes >
 LQP02HQ1N1W02E , LQP02HQ1N1W02L , LQP02HQ1N1W02B

Shape



References

Packaging code	Specifications	Minimum quantity
L	φ 180mm Embossed taping	30000
B	Packing in bulk	500
E	φ 180mm Embossed taping (W8P2*) *Width : 8mm, Pocket pitch : 2mm	15000




Mass (Typ.)	
1 piece	0.000085g

Specifications

Inductance	1.1nH ± 0.05nH
Inductance test frequency	500MHz
Rated current (Itemp) (Based on Temperature rise)	850mA
Max. of DC resistance	0.06Ω
Q (min.)	14
Q test frequency	500MHz
Self resonance frequency (min.)	12.8GHz
Operating temperature range (Self-temperature rise is not included)	-55°C to 125°C
Series	LQP02HQ_02

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.