


# LQW2BHN6N8D03#

# indicates a package specification code.



< List of part numbers with package codes >  
 LQW2BHN6N8D03L , LQW2BHN6N8D03K

## Shape



L size	2.0 ±0.2mm
W size	1.5 ±0.2mm
T size	1.7 +0.08/-0.1 mm
Size code in inch (mm)	0805 (2015)

## References

Packaging code	Specifications	Minimum quantity
L	φ 180mm Embossed taping	2000
K	φ330mm Embossed taping	7500

Mass (Typ.)	
1 piece	0.009g

## Specifications


Inductance	6.8nH ±0.5nH
Inductance test frequency	100MHz
Rated current (Itemp) (Based on Temperature rise)	680mA
Max. of DC resistance	0.11Ω
Q (min.)	20
Q test frequency	250MHz
Self resonance frequency (min.)	5400MHz
Operating temperature range (Self-temperature rise is not included)	-40°C to 85°C
Series	LQW2BHN_03

### Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

**Chart of characteristic data (The charts below may show another part number which shares its characteristics.)**

▪ Inductance-Frequency characteristics (Typ.)



▪ Q-Frequency characteristics (Typ.)



**⚠ Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.