

PRODUCT-DETAILS

T5H 630 PR221DS-LS/I In=630 3p F F

T5H 630 PR221DS-LS/I In=630 3p F F



General Information

Extended Product Type	T5H 630 PR221DS-LS/I In=630 3p F F
Product ID	1SDA054412R1
EAN	8015644555108
Catalog Description	T5H 630 PR221DS-LS/I In=630 3p F F
Long Description	C.BREAKER TMAX T5H 630 FIXED THREE-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC PR221DS-LS/I R 630

Ordering

EAN	8015644555108
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

Dimensions

Product Net Width	140 mm
Product Net Height	205 mm
Product Net Depth / Length	103.5 mm
Product Net Weight	4.807 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	248 mm
Package Level 1 Height	240 mm
Package Level 1 Depth / Length	285 mm
Package Level 1 Gross Weight	5.1 kg
Package Level 1 EAN	8015644555108

Additional Information

Electrical Durability	5000 cycle 60 cycles per hour
Mechanical Durability	20000 cycle 120 cycles per hour
Number of Poles	3
Power Loss	at Rated Operating Conditions per Pole 41 W
Product Main Type	SACE Tmax T
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current (I_n)	Main Circuit 630 A
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(220 V AC) 100 kA (230 V AC) 100 kA (380 V AC) 70 kA (400 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 65 kA (500 V AC) 50 kA (690 V AC) 40 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(220 V AC) 100 kA (230 V AC) 100 kA (380 V AC) 70 kA (400 V AC) 70 kA (415 V AC) 70 kA (440 V AC) 65 kA (500 V AC) 50 kA (690 V AC) 40 kA (250 V DC) 2 Poles in Series 70 kA (500 V DC) 2 Poles in Series 50 kA (750 V DC) 3 Poles in Series 36 kA
Rated Uninterrupted Current (I_u)	630 A
Release Type	EL
Standards	IEC
Sub-type	T5
Suitable For	T5
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Fixed Circuit-Breakers Front
Test Voltage Max (U_{test})	3500 V
Test Voltage at Industrial Frequency for 1 Minute	3500 V
Version	F

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210004D0203
Declaration of Conformity - CE	1SDL000165R0005
Environmental Information	1SDL000143R0
GL Certificate	1SDL000163R0062
Instructions and Manuals	1SDH000437R0001
Instructions and Manuals (Part 2)	ITSCE-RH0100001
RoHS Information	1SDL000200R0001

Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

