

---

**PRODUCT-DETAILS****MP1-30W****MP1-30W Pushbutton**

---

**General Information**

|                       |  |
|-----------------------|--|
| Extended Product Type | MP1-30W  |
| Product ID            | 1SFA611100R3005  |
| EAN                   | 7320500261293  |
| Catalog Description   | MP1-30W Pushbutton   |
| Long Description      | Modular Pushbutton - Momentary - Flush - White - Non-illuminated - Chrome metal - No contact block |

---

**Ordering**

|                        |               |
|------------------------|---------------|
| E-Number (Sweden)      | 3715105       |
| EAN                    | 7320500261293 |
| Minimum Order Quantity | 10 piece      |
| Customs Tariff Number  | 8536501999    |

---

**Dimensions**

|                            |          |
|----------------------------|----------|
| Product Net Width          | 0.029 m  |
| Product Net Height         | 0.029 m  |
| Product Net Depth / Length | 0.033 m  |
| Product Net Weight         | 0.024 kg |

## Container Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 1 piece       |
| Package Level 1 Width          | 0.11 m        |
| Package Level 1 Height         | 0.029 m       |
| Package Level 1 Depth / Length | 0.15 m        |
| Package Level 1 Gross Weight   | 0.026 kg      |
| Package Level 1 EAN            | 7320500261293 |

## Environmental

|                         |  |
|-------------------------|--|
| Ambient Air Temperature | Operation -25 ... +70 °C<br>Storage -30 ... +85 °C |
| RoHS Status             | Following EU Directive 2011/65/EU                  |

## Additional Information

|                       |                              |
|-----------------------|------------------------------|
| Actuator Type         | Flush                        |
| Bezel Material        | Chrome Metal                 |
| Block                 | No contact block             |
| Color                 | White                        |
| Degree of Protection  | Front IP66<br>Terminals IP20 |
| Function              | Momentary                    |
| Illumination          | Non-illuminated              |
| Mechanical Durability | 2 million                    |
| Product Main Type     | MP1                          |
| Product Name          | Pushbutton                   |
| Product Range         | Modular                      |
| Product Type          | MP                           |
| RoHS Date             | 0635 4                       |

## Certificates and Declarations (Document Number)

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SFC151007C02_  |
| Declaration of Conformity - CE    | 2CMT2015-005452 |
| Environmental Information         | 1SFC151010D0201 |
| Instructions and Manuals          | 1SFC151011M0201 |
| RoHS Information                  | 2CMT2015-005452 |

## Classifications

|                            |  |
|----------------------------|--|
| ETIM 4                     | EC002024 - Accessories for control circuit devices |
| ETIM 5                     | EC000221 - Front element for push button           |
| ETIM 6                     | EC000221 - Front element for push button           |
| ETIM 7                     | EC000221 - Front element for push button           |
| Object Classification Code | S  |
| UNSPSC                     | 39121512   |
| WEEE Category              | Product Not in WEEE Scope                          |

---

## Categories

---

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

