


PRODUCT-DETAILS

# SR2-SRN6420VK

## ENCLOSURE GLASS DOOR 600X400X200 7035



### General Information

Extended Product Type	SR2-SRN6420VK
Product ID	SRN6420VK
EAN	8015646753656
Catalog Description	ENCLOSURE GLASS DOOR 600X400X200 7035
Long Description	Enclosure with glazed door 600x400x200mm (HxWxD)

### Ordering

EAN	8015646753656
Minimum Order Quantity	1 piece
Customs Tariff Number	85381000

### Dimensions

Product Net Width	400 mm
Product Net Height	600 mm
Product Net Depth / Length	200 mm
Product Net Weight	11 kg

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.415 m
Package Level 1 Height	0.220 m
Package Level 1 Depth / Length	0.620 m
Package Level 1 Gross Weight	11.500 kg
Package Level 1 EAN	8015646753656

---

### Additional Information

Color	Grey
Construction Material	Galvanized steel
Cover Plate Type	Door
Degree of Protection	IP65
Housing Material	Steel
Interior Depth	183,5 mm
Mounting Type	Surface mounted (plaster)
Order Multiple	1 piece
Product Main Type	SR2 Enclosures
Product Name	Control and Automation Board
Protection Class	Grounded
Suitable for Product Class	SR2
Surface Finishing	Powder coating

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1STC804013D0203
Declaration of Conformity - CE	not applicable
Environmental Information	1STC804013D0203
Instructions and Manuals	1STM6041230001
RoHS Information	1STC860027

---

### Classifications

ETIM 4	EC000200 - Enclosure for control circuit devices
ETIM 5	EC000200 - Enclosure for control circuit devices
ETIM 6	EC000058 - Empty cabinet
ETIM 7	EC000058 - Empty cabinet
Object Classification Code	U
WEEE Category	Product Not in WEEE Scope

---

### Categories

Low Voltage Products and Systems → Enclosures → General Purpose Enclosures

