


## Filler plugs - ME B-22,5 MKDSO KMGY - 2908498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, Filler plug for unoccupied terminal points, color: light gray (7035)

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 361501
GTIN	4017918361501
Weight per Piece (excluding packing)	1.100 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Item properties

Brief article description	Filler plugs
Type	ME B-22,5 MKDSO KMGY
Order No.	2908498
Housing type	DIN rail housing
Type	Filler plug for unoccupied terminal points

#### Material data

Color (RAL)	light gray (7035)
Housing material	Polyamide

#### Packaging information

Pieces per package	10
Denomination packing units	Pcs.

### Environmental Product Compliance

# Filler plugs - ME B-22,5 MKDSO KMGY - 2908498

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

## Approvals

### Approvals

---

Approvals

UL Recognized

---

## Filler plugs - ME B-22,5 MKDSO KMGY - 2908498

### Approvals

Ex Approvals

---

#### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868