


Filler plugs - ME MAX B-22,5 BUGY - 2200736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, Filler plug for unoccupied terminal points, width: 20 mm, height: 21.6 mm, color: blue grey (7031)

Key Commercial Data

Packing unit	10 pc
Minimum order quantity	250 pc
GTIN	 4 046356 666459
GTIN	4046356666459
Weight per Piece (excluding packing)	1.100 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Item properties

Brief article description	Filler plugs
Type	ME MAX B-22,5 BUGY
Order No.	2200736
Housing type	DIN rail housing
Type	Filler plug for unoccupied terminal points
Mounting type	Latching

Dimensions

Width [w]	20 mm
Height [h]	21.6 mm

Material data

Color (RAL)	blue grey (7031)
Flammability rating according to UL 94	V0
Housing material	Polyamide

Filler plugs - ME MAX B-22,5 BUGY - 2200736

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

General information

Type of note	Assembly instruction:
Note	Refer to the data sheet for the range in the download area.

Packaging information

Pieces per package	10
Denomination packing units	Pcs.
Outer packaging type	Resealable bag

Standards and regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
-------------	----------

Filler plugs - ME MAX B-22,5 BUGY - 2200736

Classifications

UNSPSC

UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------
