

Cover - ME-IO 18,8 MC 8U TRANS - 2202627


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, 8U, Marking lid, width: 18.8 mm, height: 110.95 mm



Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 055626 210902
GTIN	4055626210902
Weight per Piece (excluding packing)	9.660 g
Custom tariff number	85389099
Country of origin	China

Technical data

Item properties

Brief article description	Cover
Type	ME-IO 18,8 MC 8U TRANS
Order No.	2202627
Housing type	DIN rail housing
Type	8U
Mounting type	Snap in

Dimensions

Width [w]	18.8 mm
Height [h]	110.95 mm

Material data

Color (RAL)	transparent
Flammability rating according to UL 94	V0
Housing material	Polyamide

Cover - ME-IO 18,8 MC 8U TRANS - 2202627

Technical data

PCB data

Mounting position	Vertical (horizontal DIN rail)
-------------------	--------------------------------

Packaging information

Pieces per package	5
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Cover - ME-IO 18,8 MC 8U TRANS - 2202627

Approvals


Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC			B.01742
-----	--	--	---------

Accessories

Additional products

Housing cover - ME-IO 18,8 C 2U MC 7035 - 2202616



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 2U MC10 7035 - 2202582



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, color: light gray (7035)

Housing cover - ME-IO 18,8 C 2U MC18 7035 - 2202581



DIN rail housing, 2U for marking lid, Housing cover, width: 18.9 mm, height: 21.9 mm, color: light gray (7035)

Cover - ME-IO 18,8 MC 8U TRANS - 2202627

Accessories

Insert label - EMT (80X15,5)R - 0804286



Insert label, for marking the marking cover for the ME-IO housing system, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: snapped into marker carrier, lettering field size: 80 x 15.5 mm
