

Housing cover - ME-IO 56,4 C 10U 7035 - 2202662

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail housing, 10U, Housing cover, width: 56.88 mm, height: 109.8 mm, color: light gray (7035)

Key Commercial Data

Packing unit	12 pc
Minimum order quantity	12 pc
GTIN	
GTIN	4055626218762
Weight per Piece (excluding packing)	22.140 g
Custom tariff number	85389099
Country of origin	China

Technical data

Item properties

Brief article description	Housing cover
Type	ME-IO 56,4 C 10U 7035
Order No.	2202662
Housing type	DIN rail housing
Housing series	ME-IO
Type	10U
Mounting type	Snap in

Dimensions

Width [w]	56.88 mm
Height [h]	109.8 mm

Material data

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

Housing cover - ME-IO 56,4 C 10U 7035 - 2202662

Technical data

Material data

Housing material	Polyamide
------------------	-----------

PCB data

Mounting position	Vertical (horizontal DIN rail)
-------------------	--------------------------------

Packaging information

Pieces per package	12
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.0	27371300
eCl@ss 5.1	27371300
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals


UL Recognized / EAC

Housing cover - ME-IO 56,4 C 10U 7035 - 2202662

Approvals

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 240868
---------------	---	---	---------------

EAC			B.01742
-----	---	--	---------
