

## Conductor marking - UCT-WMCO 6,8 (23X8) - 0832107

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: clip on, cable diameter range: 6.1 ... 6.8 mm, lettering field size: 23 x 8 mm, Number of individual labels: 15

### Your advantages

- ✓ The UCT-WMCO ... UniCard labeling range includes markers for the subsequent labeling of conductors by simply snapping on
- ✓ Large-surface labeling option in a space-saving design
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ Secure tight fit even in the event of vibrations
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key Commercial Data

Packing unit	4 pc
Minimum order quantity	4 pc
GTIN	 4 055626 258669
GTIN	4055626258669
Weight per Piece (excluding packing)	16.480 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Length (b)	23 mm
Width (a)	8 mm
Cable diameter	6.1 mm ... 6.8 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

# Conductor marking - UCT-WMCO 6,8 (23X8) - 0832107

## Technical data

### General

Color	white
Type	Card form
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	15
Number of individual labels per row	5
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	clip on
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	32.4 %
R22	HL 1 - HL 3
R23	HL 1 - HL 3
R24	HL 1 - HL 3

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 9.0	27400401

# Conductor marking - UCT-WMCO 6,8 (23X8) - 0832107

## Classifications

### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

## Accessories

### Accessories

#### Magazine

Magazine - TMP-UCT-MAG29 - 0803373



Magazine for the THERMOMARK PRIME printer, for accommodating UCT-WMCO ... (23xX)

Magazine - TMP-UCT-MAG29 - 0803373



Magazine for the THERMOMARK PRIME printer, for accommodating UCT-WMCO ... (23xX)