

## Conductor marker - UC-WMC 7,5 (30X8) - 0819673

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: clip on, cable diameter range: 5 ... 7.5 mm, lettering field size: 30 x 8 mm, Number of individual labels: 6

### Your advantages

- ✓ The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- ✓ Can be clipped on even after wiring has been completed
- ✓ One-handed mounting
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ Two labeling areas that are clearly legible at all times
- ✓ The markers support multi-line labeling
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts

### Key Commercial Data

|                                      |                     |
|--------------------------------------|---------------------|
| Packing unit                         | 5 pc                |
| Minimum order quantity               | 5 pc                |
| GTIN                                 | <br>4 046356 152525 |
| GTIN                                 | 4046356152525       |
| Weight per Piece (excluding packing) | 11.000 g            |
| Custom tariff number                 | 39269097            |
| Country of origin                    | Poland              |

### Technical data

#### Dimensions

|                |                 |
|----------------|-----------------|
| Length (b)     | 30 mm           |
| Width (a)      | 8 mm            |
| Cable diameter | 5 mm ... 7.5 mm |

# Conductor marker - UC-WMC 7,5 (30X8) - 0819673

## Technical data

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

### General

|   |                                     |
|---|-------------------------------------|
| Color   | white                               |
| Type  | Card form                           |
| Components  | free from silicone and halogen      |
| Flammability rating according to UL 94                              | V2                                  |
| Material  | PA                                  |
| RoHS compliant  | Yes                                 |
| Wipe resistance   | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels   | 6                                   |
| Number of individual labels per row                                 | 2                                   |
| Printability  | UV LED technology                   |
|   | Plotter                             |
| Device  | 5147999 BLUEMARK CLED               |
|   | 5144615 CMS-P1-PLOTTER              |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type   | clip on                             |
| Result  | Test passed                         |
| Oxygen index (DIN EN ISO 4589-2)                                    | 28,2%                               |
| Class I   | 3                                   |
| Class F   | 2                                   |
| R22   | HL 1 - HL 2                         |
| R23   | HL 1 - HL 2                         |
| R24   | HL 1 - HL 2                         |
| Min. cross section  | 6 mm <sup>2</sup>                   |
| Max. cross section  | 16 mm <sup>2</sup>                  |
| AWG min   | 10                                  |
| AWG max   | 6                                   |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# Conductor marker - UC-WMC 7,5 (30X8) - 0819673

## Technical data

### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | V2 |
|--|----|

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27400400 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001530 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

## Accessories

Accessories

Magazine

## Conductor marker - UC-WMC 7,5 (30X8) - 0819673

### Accessories

Magazine - P1 UC-MAG 3 - 5146095



Magazine, for CMS-P1-PLOTTER, for accommodating UC-WMC 7,5...

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>