

Profile - UM122 SET 15,7CM BK S857 - 2202596

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Press-drawn section housings, Basic profile, length: 157 mm




Your advantages

- ✔ Item is from the UM-BASIC/UM-PRO product range
- ✔ PVC press-drawn section (UM-BASIC) or PA (UM-PRO)
- ✔ Available in individual lengths
- ✔ Available in the overall widths of 72 mm, 108 mm, and 122 mm
- ✔ Variety of connection technologies
- ✔ Can be mounted on the DIN rail



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 055626 164724
GTIN	4055626164724
Weight per Piece (excluding packing)	110.800 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Product properties

Brief article description	Profile
Type	UM122 SET 15,7CM BK S857
Order No.	2202596
Housing type	Press-drawn section housings
Type	Basic profile

Profile - UM122 SET 15,7CM BK S857 - 2202596

Technical data

Dimensions

Length	15.7 cm
--------	---------

Material specifications

Color (RAL)	black
Flammability rating according to UL 94	V0

Packaging specifications

Pieces per package	10
Denomination packing units	Pcs.

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501