

## Cutting tool - CF CRIMPHANDY CUTTER - 1212520

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cutting unit, for CF CRIMPHANDY, for stranded copper wires from 0.5 - 1.5 mm<sup>2</sup>, incl. receptacle tray

### Your advantages

- Belt pouch for the CRIMPHANDY

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589529
GTIN	4046356589529
Weight per Piece (excluding packing)	129.000 g
Custom tariff number	84679900
Country of origin	Germany

### Technical data

#### General

Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1.5 mm <sup>2</sup>

#### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Classifications

#### eCl@ss

eCl@ss 10.0.1	17139201
---------------	----------

# Cutting tool - CF CRIMPHANDY CUTTER - 1212520

## Classifications

### eCl@ss

eCl@ss 4.0	21043074
eCl@ss 4.1	21043074
eCl@ss 5.0	21043290
eCl@ss 5.1	21059090
eCl@ss 6.0	21049200
eCl@ss 7.0	21049290
eCl@ss 9.0	17139201

### ETIM

ETIM 4.0	EC001186
ETIM 5.0	EC002778
ETIM 6.0	EC002778
ETIM 7.0	EC002778

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	27111518
UNSPSC 13.2	39121410
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01549
-----	---	--------------------------

