

Memory - CF FLASH 256MB APPLIC A - 2988793

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Program and configuration memory, plug-in, 256 MB with license key for function block libraries, e.g., for SNMP, SQL, wireless, motion functions, etc.

Product Description

Program and configuration memory for storing the application program and other files in the file system of the PLC, with license key for the function block libraries.

Individual function blocks from Phoenix Contact, such as those from the SQL and SNMP library or Resy+, are licensed, which means that a fee is charged for each controller on which licensed blocks are to be used. The blocks check the license stored on the controller during runtime and enable themselves or run for a limited time in demo mode.

Examples:

- Basic control functions for PID controllers with delay time constant in the D component
- Data transfer between the controller and SQL database with event-driven access to tables by means of SQL communication and Data Manipulation Language (DML)
- IT library for sending e-mails with the SMTP function, with DHCP client, DNS, and an FTP client function
- Secure, event-oriented, and inexpensive monitoring of all distributed plants via Ethernet as well as via serial interfaces

Please observe the specified performance data of your controller(s) and check that it/they are suitable for your application.


For users who do not use the function block libraries, the program and configuration memory is also available without a license as an option.

Your advantages

- Program and configuration memory, plug-in, with license key for function block libraries.
- For storing application programs and other files in the file system of the PLC
- License key for the function block libraries



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 332590
GTIN	4046356332590
Weight per Piece (excluding packing)	14.800 g
Custom tariff number	85235190
Country of origin	Germany
Note	Made to Order (non-returnable)

Memory - CF FLASH 256MB APPLIC A - 2988793

Technical data

Dimensions

Height	42.8 mm
Depth	3.3 mm
Width	36.4 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Weight	9 g
Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	27242200
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

ETIM

ETIM 3.0	EC000192
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005
UNSPSC 18.0	32101606

Memory - CF FLASH 256MB APPLIC A - 2988793

Classifications

UNSPSC

UNSPSC 19.0	32101606
UNSPSC 20.0	32101606
UNSPSC 21.0	32101606