

Pneumatic contact - HC-M-PN2-6,00-BU-V - 1676776


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Pneumatic socket with valve, for HC-M-PN2 module, internal hose diameter of 6.0 mm



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 129408
GTIN	4017918129408
Weight per Piece (excluding packing)	1.710 g
Custom tariff number	39174000
Country of origin	United States

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mechanical characteristics

Contact diameter	8 mm
Operating pressure	8.00 bar
Internal diameter of pressure hose connection	6 mm
Insertion/withdrawal cycles	≥ 500

General

Series	HC-M-02-PN
Integrated valve	Yes
Color	black
Connection method	Hose connection

Material data

Pneumatic contact - HC-M-PN2-6,00-BU-V - 1676776

Technical data

Material data

Contact material	Delrin acetal
------------------	---------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27440192
eCl@ss 4.0	27140800
eCl@ss 4.1	27140800
eCl@ss 5.0	27143400
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440205
eCl@ss 8.0	27440205
eCl@ss 9.0	27440192

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000438
ETIM 6.0	EC000438
ETIM 7.0	EC000438

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121522
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

Approvals

Approvals

Pneumatic contact - HC-M-PN2-6,00-BU-V - 1676776

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	--	--------------------------

Accessories

Accessories

Pneumatic insert, modular

Contact insert module - HC-M-02-PN-M-F - 1417434



Contact insert module, number of positions: 2, Socket, Pin, application: Pneumatics, for internal hose diameter of 6 mm

Gasket - HC-M-PN2-ERSORI - 1408216



Replacement O-ring for HC-M-PN2...ST pneumatic pin contacts

Additional products

Pneumatic contact - HC-M-PN2-6,00-ST - 1676750



Pneumatic pin, for HC-M-PN2 module, internal hose diameter of 6.0 mm
