

## Insert label - PMLP-RFID/HF (90X38) - 0830956

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Insert label with integrated RFID-HF transponder, matt, white, unmarked, can be printed with: BLUEMARK CLED, mounting type: adhesive, lettering field size: 110 x 38 mm



### Your advantages

- ✓ The PMP-RFID ... system marking range includes markers that can be fitted into existing CARRIER-PMP... label frames
- ✓ Additional information can be written to the integrated RFID-HF transponder
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The markers are located in a frame and can be marked quickly and easily with the BLUEMARK CLED
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 912297
GTIN	4046356912297
Weight per Piece (excluding packing)	20.010 g
Custom tariff number	85235200
Country of origin	Sweden
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	38 mm
Width (a)	90 mm

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
---------------------------------	------------------

#### General

## Insert label - PMLP-RFID/HF (90X38) - 0830956

### Technical data

#### General

Color	white
Components	Free from silicone and cadmium
Flammability rating according to UL 94	V0
Material	PVC/PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Adhesive	Acrylic
Printability	UV LED technology
Device	5147999 BLUEMARK CLED
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	adhesive

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

## Insert label - PMLP-RFID/HF (90X38) - 0830956

### Classifications

#### ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

##### Filler plug

Filler plugs - RVT-PA 3,5 BK - 0830959



Plastic pop rivets

---

### Labeled systems marker

Insert label - PMST (9X38) - 0830960

Insert label, white, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



Insert label - PMST (9X38) GN - 0830961

Insert label, green, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



## Insert label - PMLP-RFID/HF (90X38) - 0830956

### Accessories

#### Insert label - PMST (9X38) RD - 0830962

Insert label, red, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) GY - 0830963

Insert label, gray, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) YE - 0830964

Insert label, yellow, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) BK - 0830965

Insert label, black, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) OG - 0830966

Insert label, orange, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



## Insert label - PMLP-RFID/HF (90X38) - 0830956

### Accessories

#### Insert label - PMST (9X38) VT - 0830967

Insert label, violet, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) BN - 0830968

Insert label, brown, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



#### Insert label - PMST (9X38) BU - 0830969

Insert label, blue, pre-printed, mounting type: screw, rivet, lettering field size: 9 x 38 mm, Number of individual labels: 1



### Marker carriers

#### Marker carriers - CARRIER-PMP (108X38) - 0830958

Marker carriers, black, unlabeled, mounting type: screw, rivet, lettering field size: 90 x 38 mm

