

Terminal PC - MMT 8017S WES7 - 2404636

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Terminal PC with 43,2 cm / 17"-TFT-display (Capacitive multi-touch screen), 1920 x 1080 pixel(s) (Full HD), Intel® Celeron® 2980U 1,60 Ghz, 1x USB 2.0, 2x USB 3.0 (one of which is led outside from the back), 2x Ethernet (10/100/1000 Mbps), RJ45, Windows® Embedded Standard 7 (64-Bit) and user software: without user software. (bus system:)



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626399058
Weight per Piece (excluding packing)	8,000.000 g
Custom tariff number	84715000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Outer dimensions: width, height, depth	431 mm x 261 mm x 68 mm
--	-------------------------

Display

Display	43,2 cm / 17"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	Capacitive multi-touch screen
Backlighting	LED

Computer data

Processor	Intel® Celeron® 2980U 1,60 Ghz
Cooling	passive

Terminal PC - MMT 8017S WES7 - 2404636

Technical data

Computer data

Operating system	Windows® Embedded Standard 7 (64-Bit)
User software	without user software
RAM	4 GB DDR3
Mass storage	mSATA SSD (MLC), 128 GB
Network	2x Ethernet (10/100/1000 Mbps), RJ45
Interfaces	1x USB 2.0
	2x USB 3.0 (one of which is led outside from the back)
Monitor output	1x DisplayPort
	1x HDMI

General

Housing material	Stainless steel, fully enclosed
------------------	---------------------------------

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	0 °C ... 50 °C
Permissible humidity (operation)	10 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 85 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Device supply

Power supply unit	24 V DC +/- 20 %
-------------------	------------------

Standards and Regulations

Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Classifications

eCl@ss

eCl@ss 4.0	27250315
eCl@ss 4.1	27250315
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242301
eCl@ss 8.0	19200101
eCl@ss 9.0	19200101

ETIM

ETIM 4.0	EC001413
ETIM 5.0	EC001413

Terminal PC - MMT 8017S WES7 - 2404636

Classifications

ETIM

ETIM 6.0	EC001413
ETIM 7.0	EC001413

UNSPSC

UNSPSC 13.2	43211508
UNSPSC 18.0	43211508
UNSPSC 19.0	43211508
UNSPSC 20.0	43211508
UNSPSC 21.0	43211508

Accessories

Accessories

Mounting material

Holder - MMT VESA ADAPTER - 2404637



Accessory, mount according to VESA-MIS-75 for the MMT 8017 terminal PC