

## End cover - HC-ALU 6-161 COVER GY - 2200906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Profile housing, Side part, color: gray, width: 190.4 mm, height: 58 mm

### Your advantages

- ✔ Item is from the HC-ALU product range
- ✔ Aluminum press-drawn section
- ✔ Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- ✔ Available in overall widths 53.5 mm ... 161 mm
- ✔ Degree of protection up to IP65
- ✔ Usable as handheld and wall housing
- ✔ Optional EMC seals available



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 716789
GTIN	4046356716789
Weight per Piece (excluding packing)	329.300 g
Custom tariff number	76169910
Country of origin	Hungary
Note	Made to Order (non-returnable)

### Technical data

#### General

Housing type	Profile housing
Color (RAL)	gray

#### Dimensions

Height	58 mm
Width	190.4 mm

## End cover - HC-ALU 6-161 COVER GY - 2200906

### Technical data

#### Dimensions

Depth	161 mm
-------	--------

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

#### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501