


# Insertion plate - ME MAX 22,5 PLATE BUGY MC-001 - 2203605

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

DIN rail housing, Insertion plate



## Key Commercial Data

Packing unit	10 pc
Minimum order quantity	50 pc
GTIN	 4 055626 407500
GTIN	4055626407500
Weight per Piece (excluding packing)	1.470 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Item properties

Brief article description	Insertion plate
Type	ME MAX 22,5 PLATE BUGY MC-001
Order No.	2203605
Housing type	DIN rail housing
Type	Insertion plate

### Material data

Color (RAL)	blue grey
Insulating material	V0
Housing material	Polyamide

### Packaging information

Pieces per package	10
Denomination packing units	Pcs.

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# Insertion plate - ME MAX 22,5 PLATE BUGY MC-001 - 2203605

## Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
----------	----------

## Approvals

Approvals

---

Approvals


UL Recognized

---

Ex Approvals

---

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	---	---	---------------

---