

Antenna splitter - RAD-SPL-2-N/N - 2702293

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna splitter, frequency range: 0.3 GHz ... 6 GHz, degree of protection: IP65, connection: 3 x N (female), suitable connection cable for the antenna connection (Order No. 2700677)




Product Description

2-way distributor for antenna signals (antenna splitter), type N connector (female) on the two upper ends and type N (female) on the lower end



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 079073
GTIN	4055626079073
Weight per Piece (excluding packing)	69.000 g
Custom tariff number	85366910
Country of origin	China

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Ambient temperature (storage/transport)	-70 °C ... 100 °C
Degree of protection	IP65, when installed

General

Housing material	Brass (CuZn)
------------------	--------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Antenna splitter - RAD-SPL-2-N/N - 2702293

Classifications

eCl@ss

eCl@ss 5.0	19079100
eCl@ss 5.1	19079100
eCl@ss 7.0	19070417
eCl@ss 8.0	19070417
eCl@ss 9.0	19070417

ETIM

ETIM 5.0	EC001135
ETIM 6.0	EC001135
ETIM 7.0	EC001135

Accessories

Accessories

Coaxial cable

Antenna cable - FL LCX PIG-EF142-N-N - 2700677



Antenna cable, outside diameter: 5 mm (0.2 in.), inner conductor: stranded, attenuation: 0.3 / 0.5 / 0.8 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2 x N (male), cable length: 0.5 m (1.6 ft.)