

## Side element - UM108-SE BK - 2909989

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Side element, 5 mm wide, PCB width: 107.5 mm



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 419240
GTIN	4017918419240
Weight per Piece (excluding packing)	6.630 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Product properties

Brief article description	Side element
Type	UM108-SE BK
Order No.	2909989
Housing type	Press-drawn section housings
Type	Lateral element

#### Dimensions

Depth	122.6 mm
-------	----------

#### Material specifications

Color (RAL)	black
Flammability rating according to UL 94	V0

#### Packaging specifications

Pieces per package	10
Denomination packing units	Pcs.

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Side element - UM108-SE BK - 2909989

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

#### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

### Approvals

#### Approvals

---

Approvals

UL Recognized / EAC

---


Ex Approvals

---

#### Approval details

## Side element - UM108-SE BK - 2909989

### Approvals

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 240868
---------------	---	---	---------------

EAC			B.01742
-----	---	--	---------