

PRODUCT-DETAILS

T6 W FP 3p EF

T6 W FP 3p EF



General Information

Extended Product Type	T6 W FP 3p EF
Product ID	1SDA060384R1
EAN	8015644628154
Catalog Description	T6 W FP 3p EF
Long Description	FIXED PART WITHDRAWABLE FOR C.BREAKER TMAX THREE-POLE WITH EXTENDED FRONT TERMINALS T6

Ordering

EAN	8015644628154
Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Dimensions

Product Net Width	260 mm
Product Net Height	295 mm
Product Net Depth / Length	85.5 mm
Product Net Weight	3 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	322 mm
Package Level 1 Height	322 mm
Package Level 1 Depth / Length	439 mm
Package Level 1 Gross Weight	4.4 kg
Package Level 1 EAN	8015644628154

Additional Information

Number of Poles	3
Product Main Type	SACE Tmax T
Product Name	Accessory
Product Type	FP
Rated Operational Voltage	690 V AC 750 V DC
Rated Uninterrupted Current (I _u)	800 A
Standards	IEC 60947
Sub-type	T6
Suitable For	T6
Suitable for Product Class	Moulded Case Circuit Breakers
Terminal Connection Type	Withdrawable Circuit-Breakers Front Extended
Version	W

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC210015D0208
Declaration of Conformity - CE	1SDL000165R0006
Environmental Information	1SDL000143R0001
Instructions and Manuals	DETACHED

Classifications

ETIM 6	EC002043 - Chassis part power circuit breaker
ETIM 7	EC002043 - Chassis part power circuit breaker
Object Classification Code	Q
UNSPSC	39121100
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

