


PRODUCT-DETAILS

# XT2N 160 Ekip LS/I In=160A 3p F F

## XT2N 160 Ekip LS/I In=160A 3p F F



### General Information

Extended Product Type	XT2N 160 Ekip LS/I In=160A 3p F F
Product ID	1SDA067058R1
EAN	8015644007959
Catalog Description	XT2N 160 Ekip LS/I In=160A 3p F F
Long Description	C.BREAKER TMAX XT2N 160 FIXED THREE-POLE WITH FRONT TERMINALS AND SOLID-STATE RELEASE IN AC EKIP-LS/I R 160 A

### Ordering

E-Number (Sweden)	3182027
EAN	8015644007959
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

### Dimensions

Product Net Width	90 mm
Product Net Height	130 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	1.625 kg

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	130 mm
Package Level 1 Height	208 mm
Package Level 1 Depth / Length	145 mm
Package Level 1 Gross Weight	1.71 kg
Package Level 1 EAN	8015644007959

### Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Current Type	AC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	Nr. Operations 240 cycles per hour Nr. Operations 25000 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	CB
Rated Current ( $I_n$ )	160 A
Rated Frequency (f)	50 / 60 Hz
Rated Voltage ( $U_r$ )	690 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	8 kV
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 65 kA (230 V AC) 65 kA (240 V AC) 65 kA (380 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 36 kA (500 V AC) 30 kA (525 V AC) 20 kA (690 V AC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 65 kA (230 V AC) 65 kA (240 V AC) 65 kA (380 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 36 kA (500 V AC) 30 kA (525 V AC) 20 kA (690 V AC) 10 kA
Rated Uninterrupted Current ( $I_u$ )	160 A
Release Type	EL
Standards	IEC
Sub-type	XT2
Terminal Connection Type	Fixed Circuit-Breakers Front
Version	F

**Certificates and Declarations (Document Number)**

Data Sheet, Technical Information	1SDC210100D0204 1SDC210099D0204
Declaration of Conformity - CE	9AKK106713A5901
Environmental Information	1SDL000190R0001
GL Certificate	1SDL000163R0093
Instructions and Manuals	1SDH000721R0001
LR Certificate	1SDL000163R0100

**Classifications**

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 7	EC000228 - Power circuit-breaker for trafo/generator/installation protection
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

**Categories**

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

